

## INSTRUCTION SHEET

### Adapter ( $\phi 22$ to $\phi 30$ ) for HW1E and HW1P-5 Instructions

Confirm that the delivered product is what you have ordered. Read this instruction sheet to make sure of correct operation. Make sure that the instruction sheet is kept by the end user.



#### 1 Type

HW9Z-A30E (for  $\phi 30$  Mounting Hole)

#### 2 Specifications

Degree of Protection	IEC60529 IP65
Panel Thickness	1.6 to 3.8 mm
For Use On	HW1E and HW1P-5 only (Do not use the HW9Z-A30E with other control units.)
Material / Color	Adapter (nitrile rubber / black), Washer (brass)

#### 3 Mounting



#### 4 Notes for Operation

- The HW9Z-A30E can be used with the HW1E and HW1P-5 only. Do not use the HW9Z-A30E with other control units. When used with Jumbo Mushroom type units (HW1B-M5/V5), tightening the locking ring may damage the control unit.
- The HW9Z-A30E cannot be used with anti-rotation ring (HW9Z-RL, OGL-11, or OGL-31) or nameplate (HWA\*, HNA\*, NSA\*, NWA\*, or NA\*).
- The HW9Z-A30E does not have an anti-rotation structure. Do not turn the selector switches or other control units with an excessive force, otherwise the control units may rotate.